



## 1.0 PRODUCT DESCRIPTION

### Available Sizes:

- 14 – 24"/350 – 600 mm

### Maximum Pressure Rating:

- Fitting pressure ratings are equivalent to the pressure ratings of the coupling used to install them. (See section 7.0 for Reference Materials.)

### Function:

- Connects pipe sections, provides change in direction, and adapts sizes or components. Provides transitions between different joining methods.
- Stainless steel AGS fittings are supplied with Victaulic AGS grooves. Fittings are exclusively for use with Victaulic couplings, valves, accessories and pipe which feature ends formed with the Victaulic AGS groove profile.

### Codes and Requirements:

- Support hanger spacing corresponds to ASME B31.1 Power Piping Code and ASME B31.9 Building Services Piping Code.

## 2.0 CERTIFICATION/LISTINGS

- This system is certified to ISO 9001:2008 by the LPCB under certificate No. 104.

## 3.0 MATERIAL SPECIFICATIONS

**Wrought Fittings:** Stainless steel conforming to ASTM A 403M Grade WP, Class 5 Types 304L or 316L, as specified

**Segmentally Welded Fittings and Pipe Nipples:** Fabricated from stainless steel pipe conforming to ASTM A 312/A 312M, Types 304L or 316L, as specified.

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.

System No.		Location	
Submitted By		Date	

Spec Section		Paragraph	
Approved		Date	



















