

Style 155 Expansion Joint Application Data Sheet



09.13



Style 155 Expansion Joints are a combination of couplings and specially machined pipe nipples, joined in series to accommodate piping system expansion/contraction.

The standard units are assembled with either Style 77 or Style 75 flexible couplings. The following information is required for processing all requests for Style 155 Expansion Joints. All sections of the data form below must be completed to ensure performance requirements are satisfied.

ONCE COMPLETED, FAX OR EMAIL THIS FORM TO YOUR LOCAL VICTAULIC CUSTOMER CARE OR SALES TEAM MEMBER.

SALESMAN / DISTRIBUTOR / BRANCH CONTACT:	PROJECT REFERENCE:
---	---------------------------

PIPE SPECIFICATION:

NOMINAL DIAMETER:	ACTUAL DIAMETER:	WALL THICKNESS:	MATERIAL:
PIPE COATING:	Uncoated Galvanized Other	(Attach Specification)	
PIPE END NIPPLES:	Grooved Plain Beveled Threaded (BSP NPT)	Flanged (Class)	

SYSTEM OPERATING PARAMETERS:

SERVICE:	MAXIMUM WORKING PRESSURE:	MAXIMUM OPERATING TEMPERATURE:
COUPLING COATING:	Painted Galvanized Other	(Attach Specification)
BOLT/NUT SPECIFICATION:	Standard Metric	BOLT MATERIAL: Carbon Steel Stainless Steel

SYSTEM EXPANSION/CONTRACTION REQUIREMENTS:

MAXIMUM PIPE EXPANSION:	MAXIMUM PIPE CONTRACTION:
--------------------------------	----------------------------------

ORDERING INFORMATION:

QUANTITY REQUIRED:	DATE REQUIRED:
SPECIAL PACKAGING REQUIREMENTS:	

FOR INTERNAL USE ONLY!

ORDER NUMBER:	PART CODE NUMBER:	ENGINEERING CONTACT:
COUPLING STYLE: S/77 S/75 Other	GASKET MATERIAL: E T O L V Other	
NUMBER OF COUPLINGS:	NUMBER OF NIPPLES:	GASKET TYPE: Standard FlushSeal®
PIPE END NIPPLES:	Grooved Plain Beveled Threaded (BSP NPT)	Flanged (Class)
PIPE END NIPPLE LENGTH:	Standard Other	PIPE SCHEDULE: Std. Wgt. Hvy. Wgt. Special
EXPANSION JOINT TO BE SUPPLIED IN:	Fully Expanded Position	Fully Contracted Position Other

Contact Victaulic for additional assistance with applications requiring pipe movement compensation.