

# Victaulic® Transition Coupling for HDPE-to-Steel Pipe

## Style 907



19.10



### 1.0 PRODUCT DESCRIPTION

#### Available Sizes

- 2 – 8" IPS high-density polyethylene (HDPE) to 2 – 8"/DN50 – DN200 mm grooved steel
- 63 mm – 225 mm ISO high-density polyethylene (HDPE) to 2 – 8"/DN50 – DN200 mm grooved steel

#### Pipe Material

- HDPE pipe conforming to ASTM D3035 and ASTM F714 or ISO 4427-2 (SDR 7 – 21)

#### Maximum Working Pressure

- Meets or exceeds the pressure rating of the pipe

#### Operating Temperature

- Dependent upon pipe manufacturer rating and gasket selection
- Reference section 3.0 for gasket performance options
- Consult pipe manufacturer for pipe material performance limitations

#### Function

- Provides a single transition from plain end HDPE pipe to grooved steel sized piping system components
- Utilizes patented Installation-Ready™ technology to eliminate loose parts

#### Pipe Preparation

- For use on plain end HDPE pipe
- Prepare grooved pipe end in accordance with Publication 25.01: Original Groove System (OGS) Groove Specifications

### 2.0 CERTIFICATION/LISTINGS



#### NOTE

- See [Publication 10.01](#): Victaulic Fire Protection Approval Reference Guide for details.
- See [Publication 02.06](#): Victaulic Approvals for Potable Water Products – ANSI/NSF 61 and ANSI/NSF 372 if applicable.
- WaterMark™ certification only applies to fusion bonded epoxy-coated couplings with Grade “E” EPDM gaskets. Contact Victaulic for further details.

ALWAYS REFER TO ANY NOTIFICATIONS AT THE END OF THIS DOCUMENT REGARDING PRODUCT INSTALLATION, MAINTENANCE OR SUPPORT.

System No.		Location	
Submitted By		Date	

Spec Section		Paragraph	
Approved		Date	



### 3.0 SPECIFICATIONS – MATERIAL

**Housing:** Ductile iron conforming to ASTM A 536, Grade 65-45-12.

**Housing Coating: (specify choice)**

Standard: Orange enamel for ANSI sizes. Black enamel for ISO sizes and 5" IPS.

Optional: Fusion bonded epoxy, galvanized and other coatings are available. Contact Victaulic for details.

**Retaining Ring:** Type 316 stainless steel.

**Coupling Gasket: (specify choice<sup>1</sup>)**

**Grade "T" Nitrile**

Nitrile (Orange stripe color code). Temperature range -20°F to +180°F/-29°C to +82°C. May be specified for petroleum products, hydrocarbons, air with oil vapors, vegetable and mineral oils within the specified temperature range; not compatible for hot dry air over 140°F/ 60°C and water over +150°F/+66°C. NOT COMPATIBLE FOR USE WITH HOT WATER SERVICES OR STEAM SERVICES.

**Grade "E" EPDM**

EPDM (Green stripe color code). Temperature range -30°F to +230°F/-34°C to +110°C. May be specified for cold and hot water service within the specified temperature range plus a variety of dilute acids, oil-free air and many chemical services. UL Classified in accordance with ANSI/NSF 61 for cold +73°F/+23°C and hot +180°F/+82°C potable water service and ANSI/NSF 372. NOT COMPATIBLE FOR PETROLEUM SERVICES OR STEAM SERVICES.

**Grade "EF" EPDM**

EPDM (Green "X" color code). Temperature range -30°F to +230°F/-34°C to +110°C. May be specified for hot and cold water service within the specified temperature range plus a variety of dilute acids, oil-free air and many chemical services. Also meets hot and cold potable water requirements per DVGW, KTW, ÖVGW, SVGW, and French ACS (Crecep), approved for W534, approved for EN681-1 Type WA cold potable, and Type WB hot potable water service. NOT COMPATIBLE FOR USE WITH PETROLEUM SERVICES OR STEAM SERVICES.

**Grade "O" Fluoroelastomer**

Fluoroelastomer (Blue stripe color code). Temperature range +20°F to +300°F/-34°C to +110°C. May be specified for many oxidizing acids, petroleum oils, halogenated hydrocarbons, lubricants, hydraulic fluids, organic liquids and air with hydrocarbons. NOT COMPATIBLE FOR USE WITH HOT WATER SERVICES OR STEAM SERVICES.

<sup>1</sup> Services listed are General Service Guidelines only. It should be noted that there are services for which these gaskets are not compatible. Reference should always be made to the latest [Victaulic Gasket Selection Guide](#) for specific gasket service guidelines and for a listing of services which are not compatible.

**NOTE**

- The maximum temperature ratings shown exceed the temperature ratings for HDPE pipe. Consult individual pipe manufacturers for specific temperature limits.

**Hardware:**

**Bolts/Nuts: (specify choice<sup>2</sup>)**

Standard: Carbon steel oval neck track bolts meeting the mechanical property requirements of ASTM A449 (imperial) and ISO 898-1 Class 9.8 (M10-M16) Class 8.8 (M20 and greater). Carbon steel hex nuts meeting the mechanical property requirements of ASTM A563 Grade B (imperial - heavy hex nuts) and ASTM A563M Class 9 (metric - hex nuts). Track bolts and hex nuts are zinc electroplated per ASTM B633 ZN/FE5, finish Type III (imperial) or Type II (metric), with fluoropolymer top coat. Hardened steel washers conforming to ASTM F436 Type 3 (weathering steel).

Optional<sup>2</sup>:


2 – 4", 63 – 110 mm: Stainless steel oval neck track bolts meeting the mechanical property requirements of ASTM F593, Group 2 (316 stainless steel), condition CW. Stainless steel heavy hex nuts meeting the mechanical property requirements of ASTM F594, Group 2 (316 stainless steel), condition CW, with galling reducing coating. Hardened steel washers conforming to ASTM F436 Type 3 (weathering steel).

6 – 8"/125 – 225 mm: Stainless steel oval neck track bolts meeting the mechanical property requirements of ASTM A193 Class 2, Grade B8M. Stainless steel heavy hex nuts meeting the mechanical property requirements of ASTM A194 Grade 8M Heavy Hex, with galling reducing coating. Hardened steel washers conforming to ASTM F436 Type 3 (weathering steel).


<sup>2</sup> Optional bolts/nuts available in imperial size only

## 4.0 DIMENSIONS

### Style 907 – IPS Standard



Style 907 Pre-Assembled  
(Installation-Ready Condition)




Style 907 Joint Assembled


IPS Size		Bolt/Nut		Dimensions					Weight
Nominal inches mm	Actual Outside Diameter inches mm	Qty.	Size inches	Pre-assembled (Installation-Ready™ condition)		Joint Assembled			Approximate (Each) lb kg
				X inches mm	Y inches mm	X inches mm	Y inches mm	Z inches mm	
2 50	2.375 60.3	2	1/2 x 3/4	3.88 99	6.13 156	3.50 89	6.13 156	3.13 80	4.7 2.1
3 80	3.500 88.9	2	5/8 x 3/2	5.13 130	7.63 194	4.50 114	7.63 194	3.13 80	6.6 3.0
4 100	4.500 114.3	2	5/8 x 4/4	6.75 172	8.88 226	6.13 156	8.88 226	3.50 89	9.4 4.3
5 125	5.563 141.3	2	3/4 x 4/4	203 8.0	270 10.63	184 7.25	229 11.00	89 3.50	5.4 11.9
6 150	6.625 168.3	2	3/4 x 5	8.88 226	11.75 299	8.00 203	11.75 299	3.50 89	13.8 6.3
8 200	8.625 219.1	2	3/4 x 6/4	11.63 295	14.13 359	10.38 264	14.75 375	3.88 99	21.4 9.7

## 4.1 DIMENSIONS

### Style 907 – ISO Standard



Style 907 Pre-Assembled  
(Installation-Ready Condition)



Style 907 Joint Assembled

ISO Size HPDE Plain End x Grooved End			Bolt/Nut		Dimensions						Weight
Nominal mm	Qty.	Size <sup>3</sup> mm inches	Pre-assembled (Installation-Ready™ condition)		Joint Assembled			Approximate (Each) kg lb			
			X mm inches	Y mm inches	X mm inches	Y mm inches	Z mm inches				
63 x 60.3	2	M12 x 83 ½ x 3¼	105 4.13	156 6.13	89 3.50	156 6.13	80 3.13	2.2 4.9			
75 x 73.0	2	M16 x 83 5/8 x 3¼	124 4.88	178 7.00	111 4.38	191 7.50	80 3.13	2.7 5.9			
90 x 88.9	2	M16 x 102 5/8 x 4	133 5.25	194 7.63	118 4.63	191 7.50	80 3.13	3.0 6.5			
110 x 114.3	2	M16 x 102 5/8 x 4	159 6.25	229 9.00	143 5.63	229 9.00	89 3.50	4.4 9.6			
125 x 114.3	2	M20 x 108 ¾ x 4¼	181 7.13	254 10.00	163 6.38	267 10.50	89 3.50	5.1 11.3			
140 x 141.3	2	M20 x 108 ¾ x 4¼	203 8.0	270 10.63	184 7.25	229 11.00	89 3.50	5.4 11.9			
160 x 168.3	2	M20 x 127 ¾ x 5	216 8.50	292 11.50	194 7.63	292 11.50	89 3.50	5.8 12.8			
180 x 168.3	2	M20 x 127 ¾ x 5	241 9.50	308 12.13	219 8.63	321 12.63	92 3.63	6.8 15.0			
200 x 219.1	2	M20 x 159 ¾ x 6¼	289 11.38	365 14.38	260 10.25	381 15.00	99 3.88	9.8 21.7			
225 x 219.1	2	M20 x 159 ¾ x 6¼	299 11.75	365 14.38	270 10.63	381 15.00	99 3.88	10.0 22.0			

<sup>3</sup> Metric bolts/nuts standard, with the exception of North American, South American, and Australian shipments, where imperial sizes are standard.

## 5.0 PERFORMANCE

### Style 907 – IPS Standard

Pressure Rating: joints made with Style 907 couplings meet the pressure rating of the HDPE pipe.

IPS Size	PE4710 HDPE Pipe <sup>4</sup> DR					
	7	9	11	13.5	17	21
Nominal Size inches	Pressure Rating					
	psi kPa					
2 - 8	333 2295	250 1725	200 1380	160 1100	125 860	100 690

<sup>4</sup> HDPE pipe conforming to ASTM D3035 and F714 at 73°F/23°C. Reference plastic pipe manufacture data for derating factors at other temperatures.

**NOTE**

- Victaulic coupling gaskets have been demonstrated to seal under full (29" of Hg/3.4 kPa [absolute]) vacuum requirements. Consult the specific HDPE pipe manufacturer for their recommended limitations regarding maximum vacuum as well as the effects of temperature and pipe ovality.

## 5.1 PERFORMANCE

### Style 907 – ISO Standard

Pressure Rating: joints made with Style 907 couplings meet the pressure rating of the HDPE pipe.

ISO Size	PE100 HDPE Pipe <sup>5</sup> SDR					
	7.4	9	11	13.6	17	21
Nominal Size mm	Pressure Rating					
	Bar kPa psi					
63 – 225	25 2500 363	20 2000 290	16 1600 232	12.5 1250 182	10 1000 145	8 800 116

<sup>5</sup> HDPE pipe conforming to ISO 4427-2 at 68°F/20°C. Reference plastic pipe manufacture data for derating factors at other temperatures.

**NOTE**

- Contact Victaulic for other polyethylene materials.

## 5.2 PERFORMANCE

### Style 907 – IPS Standard

Allowable Tensile Load (ATL): joints made with Style 907 couplings can sustain tensile loads noted below.

IPS Size	Allowable Tensile Load <sup>6</sup>					
	DR					
Nominal Size inches	7	9	11	13.5	17	21
	lb N					
2	2369	1911	1599	1327	1071	878
	10540	8501	7114	5904	4765	3906
3	5146	4151	3473	2882	2327	1906
	22890	18463	15449	12821	10349	8478
4	8507	6861	5741	4765	3846	3151
	37839	30520	25539	21195	17108	14016
5	12292	10388	8692	7165	5823	4815
	54678	46208	38664	31872	25902	21418
6	18437	14871	12444	10327	8336	6829
	82013	66151	55353	45938	37081	30377
8	31200	25200	21100	17500	14100	11574
	138784	112095	93857	77844	62720	51484

## 5.3 PERFORMANCE

### Style 907 – ISO Standard

Allowable Tensile Load (ATL): joints made with Style 907 couplings can sustain tensile loads noted below.


ISO Size	Allowable Tensile Load <sup>6</sup>					
	SDR					
Nominal Size mm	7.4	9	11	13.6	17	21
	N lb					
63	11076	9360	7832	6456	5247	4297
	2490	2104	1761	1451	1179	9606
75	15702	13269	11103	9150	7437	6094
	3530	2983	2496	2057	1672	1370
90	22616	19112	15992	13182	10713	8776
	5084	4297	3595	2964	2408	1973
110	33748	28519	23864	19671	15987	13096
	7587	6411	5365	4422	3594	2944
125	43610	36854	30840	25422	20658	16921
	9804	8285	6933	5715	4644	3804
140	54678	46208	38664	31872	25902	21218
	12292	10388	8692	7165	5823	4770
160	71440	60372	50517	41641	33841	27721
	16061	13572	11357	9361	7608	6232
180	90415	76407	63934	52698	42827	35053
	20326	17177	14373	11847	9628	7887
200	111561	94276	78889	65029	52849	43290
	25080	21194	17735	14619	11881	9732
225	141271	119381	99898	82345	66919	54820
	31759	26838	22458	18512	15044	12324

<sup>6</sup> Allowable tensile loads shown are for straight pulling for a maximum period of one half hour at ambient temperature (68°F/20°C).

## 5.4 PERFORMANCE

### Style 907 – IPS Standard

Bend Radius: joints made with Style 907 couplings can sustain a bending radius as recommended by the Plastic Pipe Institute (PPI) in the Handbook of PE Pipe (2nd ed, Chapter 7, Table 4).



IPS Size Nominal Size inches	Minimum Recommended Bend Radius DR					
	7	9	11	13.5	17	21
	inches mm					
2	48 1207	48 1207	59 1508	59 1508	64 1629	155 3937
3	70 1778	70 1778	88 2223	88 2223	95 2400	95 2400
4	90 2286	90 2286	113 2858	113 2858	122 3086	122 3086
5	111 2813	111 2813	138 3516	138 3516	149 3797	149 3797
6	133 3366	133 3366	166 4207	166 4207	179 4543	179 4543
8	173 4382	173 4382	216 5477	216 5477	233 5915	233 5915







## 5.5 PERFORMANCE

### Style 907 – ISO Standard

Bend Radius: joints made with Style 907 couplings can sustain a bending radius as recommended by the Plastic Pipe Institute (PPI) in the Handbook of PE Pipe (2nd ed, Chapter 7, Table 4).

ISO Size Nominal Size mm	Minimum Recommended Bend Radius SDR					
	7.4	9	11	13.6	17	21
	mm inches					
63	1266 50	1266 50	1582 62	1582 62	1709 67	4090 161
75	1507 59	1507 59	1884 74	1884 74	2035 80	4877 192
90	1809 71	1809 71	2261 89	2261 89	2442 96	2442 96
110	2210 87	2210 87	2762 109	2762 109	2983 117	2983 117
125	2512 99	2512 99	3140 124	3140 124	3391 134	3391 134
140	2813 111	2813 111	3516 138	3516 138	3797 149	3797 149
160	3215 127	3215 127	4019 158	4019 158	4340 171	4340 171
180	3617 142	3617 142	4521 178	4521 178	4883 192	4883 192
200	4018 158	4018 158	5022 198	5022 198	5424 214	5424 214
225	4521 178	4521 178	5652 223	5652 223	6104 240	6104 240

## 6.0 NOTIFICATIONS

 <b>WARNING</b>				
				
<ul style="list-style-type: none"> <li>• Read and understand all instructions before attempting to install, remove, adjust, or maintain any Victaulic piping products.</li> <li>• Depressurize and drain the piping system before attempting to install, remove, adjust, or maintain any Victaulic piping products.</li> <li>• Wear safety glasses, hardhat, and foot protection.</li> </ul> <p>Failure to follow these instructions may cause joint failure, resulting in death or serious personal injury and property damage.</p>				

## 7.0 REFERENCE MATERIALS

- [I-900: Victaulic HDPE Products Installation and Assembly Manual](#)
- [IT-907: Victaulic Style 907 Installation Tag](#)
- [05.01: Victaulic Gasket Selection Guide](#)
- [19.07: Victaulic Style 905 Coupling for Plain End HDPE](#)
- [19.09: Victaulic Style 908 Coupling for Double Grooved HDPE pipe](#)
- [19.11: Victaulic HDPE Plain End Fittings](#)
- [19.12: Victaulic Style 904 Flange Adapter for HDPE-to-Flanged Pipe](#)
- [29.01: Victaulic Terms and Conditions/Warranty](#)

### User Responsibility for Product Selection and Suitability

Each user bears final responsibility for making a determination as to the suitability of Victaulic products for a particular end-use application, in accordance with industry standards and project specifications, and the applicable building codes and related regulations as well as Victaulic performance, maintenance, safety, and warning instructions. Nothing in this or any other document, nor any verbal recommendation, advice, or opinion from any Victaulic employee, shall be deemed to alter, vary, supersede, or waive any provision of Victaulic Company's standard conditions of sale, installation guide, or this disclaimer.

### Intellectual Property Rights

No statement contained herein concerning a possible or suggested use of any material, product, service, or design is intended, or should be construed, to grant any license under any patent or other intellectual property right of Victaulic or any of its subsidiaries or affiliates covering such use or design, or as a recommendation for the use of such material, product, service, or design in the infringement of any patent or other intellectual property right. The terms "Patented" or "Patent Pending" refer to design or utility patents or patent applications for articles and/or methods of use in the United States and/or other countries.

### Note

This product shall be manufactured by Victaulic or to Victaulic specifications. All products to be installed in accordance with current Victaulic installation/assembly instructions. Victaulic reserves the right to change product specifications, designs and standard equipment without notice and without incurring obligations.

### Installation

Reference should always be made to the Victaulic installation handbook or installation instructions of the product you are installing. Handbooks are included with each shipment of Victaulic products, providing complete installation and assembly data, and are available in PDF format on our website at [www.victaulic.com](http://www.victaulic.com).

### Warranty

Refer to the Warranty section of the current Price List or contact Victaulic for details.

### Trademarks

*Victaulic* and all other Victaulic marks are the trademarks or registered trademarks of Victaulic Company, and/or its affiliated entities, in the U.S. and/or other countries.